

## Compact Hygiene Station DLSO-HD + EK 800 Twin

The compact hygiene station of the DLSO-HD + EK 800 TWIN line composed of two pass-through sole cleaning machines DLSO-HD and the entry control device EK 800 TWIN, both lines with a tamper-proof two hand disinfection in connection with an – after successful hand disinfection – unlocked turnstile.

A canister holder for the hand disinfectant is attached to the side of the EK 800 TWIN. The multi-functional LED light simplifies the operation of the unit and also informs the user of the fill level of the hand disinfectant.

Moreover, it signals in case of malfunction. The compact hygiene station can be attached to a plant data collection device.

The machine comes ready for connection. Siphon, joints and gaskets and small parts are not included. The walk-through sole cleaning machine is available in brush lengths 1100 and 1600 mm.

### Technical data

DLSO-HD 1500 + EK 800 TWIN Dimensions (LxDxH) 2110 x 1890 x 1850 mm Brush length 1100 mm

DLSO-HD 2000 + EK 800 TWIN Dimensions (LxDxH) 2610 x 1890 x 1850 mm Brush length 1600 mm

Electrical connection 400 V/N/PE, 50/60 Hz

Power consumption 1,25 kW

Water connection 3/4" max. 43 °C

Water outlet DN 50

